

导轨型电源供应器

DIN Eco 系列

效能之本 穩築基石

340~575V

三相交流输入

(3ENA 输入最高可达 600V)



-40~70°C

宽工作环境温度
(50°C 满功率输出)



DC OK 继电器输出 (>480W)
与 LED 指示灯

目標應用



储能系统



数据中心



纤薄且窄机身
的设计



风力发电机



电动汽车充电桩



符合全球认证
IEC/EN/UL
62368-1 / 61010-1




95%
超高
效能



4KV/2KV
浪涌
防护能力



DIN Eco 系列

系列	型号名称	PFC	输出			输入电压范围	尺寸 (毫米) (H × W × D)
			电压	电流	功率		
 <ul style="list-style-type: none"> 三相交流电输入 窄机身设计 50°C 满功率输出 4KV/2KV 浪涌防护能力 	DRL-24V120W3EN□		24 V	5.0 A	120 W	输入电压范围 3EN : 340-575 Vac 3ENA : 340-600 Vac (即将推出)	123.6 × 40 × 116.8
	DRL-24V240W3EN□			10.0 A	240 W		123.6 × 56 × 116.8
	DRL-24V480W3EN□	●		20.0 A	480 W		123.6 × 60 × 142.6
	DRL-24V960W3EN□	●		40.0 A	960 W		123.6 × 110 × 142.6
	DRL-48V120W3EN□			48 V	2.5 A		120 W
	DRL-48V240W3EN□		5.0 A		240 W	123.6 × 56 × 116.8	
	DRL-48V480W3EN□	●	10.0 A		480 W	123.6 × 60 × 142.6	
	DRL-48V960W3EN□	●	20.0 A		960 W	123.6 × 110 × 142.6	

官网

微信



www.DeltaPSU.cn

sps.reply.chn@deltaww.com