

DIN Rail Power Supplies

# DIN Eco Series

Performance at the Core,  
Built to Last

**340~575V**

3 Phase AC Input Operating  
(3ENA Input Up to 600V)



**-40~70 °C**

Wide Operating  
Ambient  
Temperature

(Full Power Up to 50°C)



DC OK Relay (>480W)  
and LED Indicator

## Target Application



ESS



Data Center



Slim & Compact  
Design



Wind Turbine



EV Charger



Meet Global Certified  
IEC/EN/UL  
62368-1 / 61010-1




**95%**  
Ultra-High  
Efficiency



**4KV/2KV**  
Surge Protection  
Capacity



# DIN Eco Series

Series	Model Name	PFC	Output			Input Voltage Range	Dimensions (mm) (H × W × D)
			Voltage	Current	Power		
 <ul style="list-style-type: none"> <li>• 3-Phase AC Input Operating</li> <li>• Slim &amp; Compact Design</li> <li>• Full Power Up to 50°C</li> <li>• Surge Protection Capacity 4KV / 2KV</li> </ul>	DRL-24V120W3EN□		24 V	5.0 A	120 W	3EN : 340-575 V <sub>AC</sub> 3ENA : 340-600 V <sub>AC</sub> (Coming Soon)	123.6 × 40 × 116.8
	DRL-24V240W3EN□			10.0 A	240 W		123.6 × 56 × 116.8
	DRL-24V480W3EN□	●		20.0 A	480 W		123.6 × 60 × 142.6
	DRL-24V960W3EN□	●		40.0 A	960 W		123.6 × 110 × 142.6
	DRL-48V120W3EN□			48 V	2.5 A		120 W
	DRL-48V240W3EN□		5.0 A		240 W	123.6 × 56 × 116.8	
	DRL-48V480W3EN□	●	10.0 A		480 W	123.6 × 60 × 142.6	
	DRL-48V960W3EN□	●	20.0 A		960 W	123.6 × 110 × 142.6	



PSU.deltaww.com

May 2026 (Rev. 01) - All information and specifications are subjected to change without prior notice.