



# 中国国家强制性产品认证证书

证书编号：2026011002850256

## 认证委托人名称及地址

台达电子工业股份有限公司  
台湾桃园市龟山区山顶里兴邦路 31 之 1 号

## 生产者名称及地址

台达电子工业股份有限公司  
台湾桃园市龟山区山顶里兴邦路 31 之 1 号

## 生产企业名称及地址

台达电子(东莞)有限公司西南分公司  
中国广东省东莞市石碣镇蟠桃路 33 号

## 产品名称和系列、型号、规格

LED 模块用交流电子控制装置 (LED 控制装置, 独立式, 控制端口调光, 恒流模式, 自耦式,  $t_a: 50^{\circ}\text{C}$ ,  $t_c: 85^{\circ}\text{C}$ , I 类, IP66, 适宜直接安装在普通可燃材料表面, 定温热保护:  $110^{\circ}\text{C}$ )

见附页; 200-480V~ 50/60Hz

## 产品标准和技术要求

GB 17625.1-2022; GB/T 17743-2021; GB/T 19510.1-2023; GB/T 19510.213-2023

上述产品符合《强制性产品认证实施规则 照明电器》(CNCA-C10-01:2014) 的要求, 特发此证。

发证日期: 2026 年 03 月 04 日 有效期至: 2031 年 03 月 03 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验,  
也可在认监委网站 ([www.cnca.gov.cn](http://www.cnca.gov.cn)) 查询。

经中国合格评定国家认可委员会认可 CNAS C001-P



签发:

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





# 中国国家强制性产品认证证书

证书编号: 2026011002850256

证书附页: 第 1 页 共 2 页

LNA-1K8A45ABFCB ; LNA-1K8A45ABFCB1 ;

LNA-1K8A45ABFCB2 ; LNA-1K8A45ABFCB3

输入: 200-480V ~ 7.9-4.0A 1865W(Max.) 50/60Hz  $\lambda > 0.95$

输出: 1800W (Max.)(1500W Max.for 200-248V~) 1500-4500mA 150-550Vdc

Uout=600Vdc Uaux:+12Vdc 250mA

EUCO-1K8450GA ; EUCO-1K8450GA1 ;

EUCO-1K8450GA2 ; EUCO-1K8450GA3

输入: 200-480V ~ 7.9-4.0A 1865W(Max.) 50/60Hz  $\lambda > 0.95$

输出: 1800W (Max.)(1500W Max.for 200-248V~) 1500-4500mA 150-550Vdc

Uout=600Vdc Uaux:+12Vdc 250mA

LNA-1K8A45ABHGB ; LNA-1K8A45ABHGB1 ;

LNA-1K8A45ABHGB2 ; LNA-1K8A45ABHGB3

输入: 200-480V ~ 7.9-4.0A 1865W(Max.) 50/60Hz  $\lambda > 0.95$

输出: 1800W (Max.)(1500W Max.for 200-248V~) 1500-4500mA 150-550Vdc

Uout=600Vdc Uaux:+24Vdc 125mA

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



# 中国国家强制性产品认证证书

证书编号: 2026011002850256

证书附页: 第 2 页 共 2 页

EUCO-1K8450GCA ; EUCO-1K8450GCA1 ;

EUCO-1K8450GCA2 ; EUCO-1K8450GCA3

输入: 200-480V ~ 7.9-4.0A 1865W(Max.) 50/60Hz  $\lambda > 0.95$

输出: 1800W (Max.)(1500W Max.for 200-248V~) 1500-4500mA 150-550Vdc

Uout=600Vdc Uaux:+24Vdc 125mA

注 1: 所有型号带辅助源, 仅用于外部调光器(用户另行配置)供电。

注 2: 输入端与调光端之间按加强绝缘考核, 输入端与辅助源之间按加强绝缘考核,

输出端与调光端之间按加强绝缘考核, 输出端与辅助源之间按加强绝缘考核, 辅助源与调光端之间按基本绝缘考核, 调光端与调光端之间满足基本绝缘的要求。

注 3: LNA-1K8A45ABFCB 系列、EUCO-1K8450GA 系列是 0-10V/PWM 调光; LNA-1K8A45ABHGB 系列、EUCO-1K8450GCA 系列是 DALI & RDM/DMX 调光。

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

**CERTIFICATE NO.:** 2026011002850256

**NAME AND ADDRESS OF THE APPLICANT**

Delta Electronics, Inc.  
No. 31-1, Xingbang Road, Shanding Village, Guishan District, Taoyuan City 333613, Taiwan ,  
P.R.China

**NAME AND ADDRESS OF THE MANUFACTURER**

Delta Electronics, Inc.  
No. 31-1, Xingbang Road, Shanding Village, Guishan District, Taoyuan City 333613, Taiwan ,  
P.R.China

**NAME AND LOCATION OF THE FACTORY**

Delta Electronics (Dongguan) Co., Ltd. Southwest Branch.  
No.33, Pantao Road, Shijie Town, Dongguan, Guangdong 523308, P. R. China

**PRODUCT NAME,MODEL AND SPECIFICATION**

A.C. Supplied Electronic Controlgear For LED Modules (LED Controlgear, Independent, Controlled  
Port Dimming, Constant Current Mode, Auto-wound Controlgear, ta:50°C, tc:85°C, Class I , IP66,  
Suitable For Direct Mounting On Normally Flammable Material Surfaces, Temperature Declared  
Thermally Protected: 110°C)  
See Appendix ; 200-480V ~ 50/60Hz

**STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023

This is to certify that the above mentioned product(s) complies with the requirements of  
implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

**Valid from:** Mar.04,2026

**Valid until:** Mar.03,2031

The certificate information and validity could be checked by scanning the QR code below or logging in to  
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



SIGNATURE:

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

CERTIFICATE NO. : 2026011002850256

Appendix: Page 1 of 2

LNA-1K8A45ABFCB ; LNA-1K8A45ABFCB1 ;

LNA-1K8A45ABFCB2 ; LNA-1K8A45ABFCB3

输入: 200-480V ~ 7.9-4.0A 1865W(Max.) 50/60Hz  $\lambda > 0.95$

输出: 1800W (Max.)(1500W Max.for 200-248V~) 1500-4500mA 150-550Vdc

Uout=600Vdc Uaux:+12Vdc 250mA

EUCO-1K8450GA ; EUCO-1K8450GA1 ;

EUCO-1K8450GA2 ; EUCO-1K8450GA3

输入: 200-480V ~ 7.9-4.0A 1865W(Max.) 50/60Hz  $\lambda > 0.95$

输出: 1800W (Max.)(1500W Max.for 200-248V~) 1500-4500mA 150-550Vdc

Uout=600Vdc Uaux:+12Vdc 250mA

LNA-1K8A45ABHGB ; LNA-1K8A45ABHGB1 ;

LNA-1K8A45ABHGB2 ; LNA-1K8A45ABHGB3

输入: 200-480V ~ 7.9-4.0A 1865W(Max.) 50/60Hz  $\lambda > 0.95$

输出: 1800W (Max.)(1500W Max.for 200-248V~) 1500-4500mA 150-550Vdc

Uout=600Vdc Uaux:+24Vdc 125mA

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

CERTIFICATE NO. : 2026011002850256

Appendix: Page 2 of 2

EUCO-1K8450GCA ; EUCO-1K8450GCA1 ;

EUCO-1K8450GCA2 ; EUCO-1K8450GCA3

输入: 200-480V ~ 7.9-4.0A 1865W(Max.) 50/60Hz  $\lambda > 0.95$

输出: 1800W (Max.)(1500W Max.for 200-248V~) 1500-4500mA 150-550Vdc

Uout=600Vdc Uaux:+24Vdc 125mA

注 1: 所有型号带辅助源, 仅用于外部调光器(用户另行配置)供电。

注 2: 输入端与调光端之间按加强绝缘考核, 输入端与辅助源之间按加强绝缘考核,

输出端与调光端之间按加强绝缘考核, 输出端与辅助源之间按加强绝缘考核, 辅助源与调光端之间按基本绝缘考核, 调光端与调光端之间满足基本绝缘的要求。

注 3: LNA-1K8A45ABFCB 系列、EUCO-1K8450GA 系列是 0-10V/PWM 调光; LNA-1K8A45ABHGB 系列、EUCO-1K8450GCA 系列是 DALI & RDM/DMX 调光。

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.