

# LED Driver

## USC4 PRO

# USC4 PRO



### Highlights & Features

- Wide range constant current design
- High AC input voltage range from 277-480Vac
- High efficiency up to 95.8%
- Wide operating temperature range -40°C to +55°C
- With IP66/IP67 protection from most outdoor applications
- Build-in Active PFC and conform to harmonic current IEC/EN 61000-3-2, Class C
- Adjustable constant current level through programmable tool
- Common mode 6kV/ differential mode 6kV surge immunity
- Suitable for Wet location
- 0-10V dimming available

### Safety Standards



### Dimensions (L x W x H):

|               |  |
|---------------|--|
| USC4-320280GA | 240 x 100 x 38 mm<br>(9.45 x 3.94 x 1.50 inch)   |
| USC4-600400GA | 308.4x116.7x50.8 mm<br>(12.14"x4.60"x2.00" inch) |

### General Description

Delta LED drivers come in different series to suit different application needs. The USC4 PRO series features program output current level. All the models come in full corrosion resistance aluminum casing and major international safety certifications. USC4 PRO series offers the capability to achieve different level of LED brightness via built-in 0-10V dimming function to meet various application and energy optimization needs. The products are designed and rigorously tested to work with various outdoor LED lighting conditions. Featuring high surge immunity (CM: 6kV, DM: 6kV) and complying to IP66/IP67 make Delta USC4 PRO series an essential part of an energy efficient LED lighting power solution for both indoor and outdoor applications.

### Model Information

USC4 PRO LED Driver

| Model Number  | Input Voltage Range | Rated Output Voltage | Program Output Current Range | Constant Power Current Range |
|---------------|---------------------|----------------------|------------------------------|------------------------------|
| USC4-320280GA | 277-480Vac Typical  | 75-152Vdc            | 1400-2800mA                  | 2100-2800mA                  |
| USC4-600400GA | 249-528Vac Range    | 150-300Vdc           | 1000-3000mA                  | 2000-3000mA                  |

### Model Numbering

| US                     | C                | 4       | - | □□□                                  | □□□  | G                           | A  |
|------------------------|------------------|---------|---|--------------------------------------|--|-----------------------------|--|
| Safety Approval<br>UL, | Constant current | Outdoor |   | Output Power<br>320:320W<br>600:600W | Max Output Current<br>280 – 2800mA<br>400 – 4000mA | Programmable output current | Variable<br>A or C:<br>0-10V DIM &<br>+12V/100mA |

# LED Driver

## USC4 PRO

### Specifications

| Model Number | USC4-320280GA | USC4-600400GA |
|--------------|---------------|---------------|
|--------------|---------------|---------------|

#### Input Ratings / Characteristics

|  |  |  |
|--|--|--|
| Normal Input Voltage                                 | 277-480Vac   |  |
| Input Voltage Range                                  | 249-528Vac   |  |
| Normal Input Frequency                               | 50-60Hz  |  |
| Input Frequency Range                                | 47-63Hz  |  |
| Max. Input Current                                   | 277Vac 1.5A  | 2.4A   |
| Efficiency 1)  | 277Vac 91.5% @ 2.8A  | 95.0% @ 2.0A   |
|  | 347Vac 93.5% @ 2.8A  | 95.2% @ 2.0A   |
|  | 480Vac 93.5% @ 2.8A  | 95.8% @ 2.0A   |
| Inrush Current<br>(Apk / 50% - $\mu$ S @ Cold Start) | 277Vac 60A/250uS   | 15A/5mS  |
|  | 347Vac 60A/250uS   | 20A/5mS  |
|  | 480Vac 80A/250uS   | 25A/5mS  |
|  | Inrush current is measured at peak of the corresponding line voltage. Source impedance per NEMA 410. |  |
| Power Factor   | > 0.9 @ 50% Load , 277-480Vac<br>>=0.95 @ Full Load , 277-480Vac                                     | > 0.9 @ 50% Load , 277-480Vac<br>>=0.95 @ Full Load , 277-480Vac |
| Total Harmonic Distortion                            | <20%@ Load >50% , 277-480Vac   |  |
| Leakage Current                                      | < 0.75mArms @ 480Vac   |  |
| Standby Power (Dim to off)                           | <1.5W @ 277-480Vac   |  |
|  | <0.5W @ 277Vac   |  |
|  | <0.6W @ 347Vac   |  |
|  | <0.7W @ 480Vac   |  |
| Input Over-Voltage                                   | N/A  |  |

1) 100% Load (typical) and tested after 30 minutes warm up.

#### Output Ratings / Characteristics

|                                 |   |                                      |
|---------------------------------|---|--------------------------------------|
| Output Voltage Range            | 75-152Vdc   | 150-300Vdc                           |
| Max. No Load Output Voltage     | 170V  | 350V                                 |
| Output Power Range              | 320W  | 600W                                 |
| Output Constant power range     | 2100 - 2800mA                                     | 2000 - 3000mA                        |
| Adjustable Output Current (AOC) | 1400 - 2800mA                                     | 1000 - 3000mA                        |
|                                 | With steps of 1mA, configurable via software      |                                      |
| Minimum Output Current          | 280mA (Min dim level)                             | 140mA (Min dim level)                |
| Current Accuracy                | $\pm$ 5% (@ Typical output current range)         |                                      |
| Line Regulation                 | $\pm$ 1% (@ 277-480Vac input)                     |                                      |
| Load Regulation                 | $\pm$ 3% (@ Min-Max output voltage)               |                                      |
| Output Current Ripple           | <10% (ripple = peak-average/average) at full load |                                      |
| Start-up Time                   | 1000ms max. @ 277-480Vac (full load)              | 1000ms max. @ 277-480Vac (full load) |
| Hold-up Time                    | 16ms typ. @ 277-480Vac (full load)                |                                      |

#### Mechanical

|                             |   |  |
|-----------------------------|---|--|
| Casing                      | Aluminum, Color : Natural   |  |
| Dimensions (L x W x H) [mm] | 240.0 x 100.0 x 38.0  |  |
|                             | 9.45 x 3.94 x 1.50  |  |
| Unit Weight [kg]            | 308.4x116.7x50.8  |  |
|                             | 12.14"x4.60"x2.00"  |  |
| Unit Weight [lb]            | 1.85  |  |
|                             | 4.07  |  |
| 3.05                        | 6.72  |  |
| Cooling System              | Convection  |  |
| Input Cable                 | Line: Brown, Neural: Blue, PE: Yellow/Green, Cable Length 300mm     | Line: Black, Neural: White, PE: Yellow/Green, Cable Length 300mm |
| Output Cable                | Positive: Brown, Negative: Blue, NTC/PRG: Black, Cable Length 300mm |  |
| Dimming Cable               | Dim(+): Purple, Dim(-): Gray, +12V: Black/White, Cable Length 300mm |  |
| Noise (30cm distance)       | Sound Pressure Level (SPL) < 24dBA class A                          |  |

# LED Driver

## USC4 PRO

|                     |               |               |
|---------------------|---------------|---------------|
| <b>Model Number</b> | USC4-320280GA | USC4-600400GA |
|---------------------|---------------|---------------|

### Environment

|                          |           |                               |                |
|--------------------------|-----------|-------------------------------|----------------|
| Ambient Temperature      | Operating | -40°C to +55°C                | -40°C to +55°C |
|                          | Storage   | -40°C to +85°C                |                |
| Maximum Case Temperature |           | +90°C                         | +80°C          |
| Relative Humidity        | Operating | 10 to 90% RH (Non-Condensing) |                |
|                          | Storage   | 5 to 95% RH (Non-Condensing)  |                |
| Environmental Locations  |           | Wet location                  |                |

### Protections

|                                   |  |         |
|-----------------------------------|--|---------|
| Over Voltage                      | 170Vrms  | 350Vrms |
|                                   | Auto-Recovery when the fault is removed                        |         |
| Overload / Overcurrent            | Reduce output current. Auto-Recovery when the fault is removed |         |
| Short Circuit                     | Auto-Recovery when the fault is removed                        |         |
| Over Temperature                  | Reduce output current. Auto-Recovery when the fault is removed |         |
| Ingress Protection Classification | IP66/IP67  |         |
| Suitable for Luminaires Class     | Class I. Insulation Class according to IEC 60598               |         |

### Reliability Data

|          |   |
|----------|---|
| Lifetime | 50,000 hours at case temp. tc & full load.<br>Refer to "Lifetime VS Case Temperature" |
|----------|---|

### Safety Standards / Directives

|                    |                                     |             |              |              |
|--------------------|-------------------------------------|-------------|--------------|--------------|
| Electrical Safety  | UL 8750, UL class P                 |             |              |              |
| CE                 | NA                                  |             |              |              |
| Material and Parts | RoHS Directive 2011/65/EU Compliant |             |              |              |
| Galvanic Isolation | Mains (Input)                       | Output/PROG | DIM ± & +12V | Earth (Case) |
| Mains (Input)      | N/A                                 | 2xU+1kV     | 2xU+1kV      | 2xU+1kV      |
| Output/PROG        | 2xU+1kV                             | N/A         | 2xU+1kV      | 2xU+1kV      |
| DIM ± & +12V       | 2xU+1kV                             | 2xU+1kV     | N/A          | 2xU+1kV      |
| Earth (Case)       | 2xU+1kV                             | 2xU+1kV     | 2xU+1kV      | N/A          |

### EMI/EMC Compliance

|  |   |
|--|---|
| FCC Title 47 Part 15 Class A             | Conducted emission Test & Radiated emission Test<br>This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: [1] this device may not cause harmful interference, and [2] this device must accept any interference received, including interference that may cause undesired Operation. |
| IEC 61000-3-2                            | Harmonic Current Emission   |
| IEC 61000-3-3                            | Voltage Fluctuation & Flicker   |
| IEC 61000-4-2                            | Electrostatic Discharge(ESD): 8 kV air discharge, 4 kV contact discharge  |
| IEC 61000-4-3                            | Radio-Frequency Electromagnetic Field Susceptibility Test-RS  |
| IEC 61000-4-4                            | Electrical Fast Transient/Burst-EFT   |
| IEC 61000-4-5<br>ANSI C82.77-5 CAT C low | Surge Immunity Test: AC Power Line: Differential Mode 6 kV, Common Mode 6 kV<br>1.2/50µs Combination Wave   |
| IEC 61000-4-6                            | Conducted Radio Frequency Disturbances test-CS  |

# LED Driver

## USC4 PRO

|                |              |
|----------------|--------------|
| IEC 61000-4-11 | Voltage Dips |
|----------------|--------------|

|                     |               |               |
|---------------------|---------------|---------------|
| <b>Model Number</b> | USC4-320280GA | USC4-600400GA |
|---------------------|---------------|---------------|

### 0-10V Dimming Specification

|                           |  |
|---------------------------|--|
| Absolute Maximum Voltage  | ± 20V  |
| Source Current            | 200µA ± 50µA   |
| Dimming Input Range       | 1) 0-10V, 1.2V (± 0.1V) is 10% of lo_set or 100mA minimum, ≥ 8.5V is 100% of lo_set.<br>2) Lower than 1.1V (± 0.1V) → DIM to OFF is programmable. 0.1V Hysteresis.<br>3) Short is 0% (DIM to OFF)<br>4) Open is 100%<br>5) See 0-10V Dimming Curve |
| Dimming Current Tolerance | ± 10% of maximum setting output current. Ex. lo_set: 1000mA, tolerance is ± 100mA.   |

### Default Settings of the Driver (can be changed with programmable tools)


|                                     |  |                         |       |
|-------------------------------------|--|-------------------------|-------|
| Adjustable Output Current (AOC)     | 2100mA   | 2000mA                  |       |
| 0-10V DIM                           | Enabled (DIM to OFF). Selectable for Min. Dim Level and Min. & Max. Dim Voltage though tools |                         |       |
| Smart Timer DIM                     | Disabled (Only one function will be enabled between 0-10V & Smart Time Dim)                  |                         |       |
| Module Temperature Protection (MTP) | Disabled. Settable though programmable tools   |                         |       |
| Constant Lumen Output (CLO)         | Disabled. Settable though programmable tools.  |                         |       |
| End of Life indication (EOL)        | Disabled. Settable though programmable tools   |                         |       |
| Auxiliary Output Voltage            | +12V Output Range  | +12Vdc (10.2 – 13.8Vdc) |       |
|                                     | +12V Output Current  | 100mA                   | 200mA |
|                                     | Maximum Output Power   | 1.2W                    | 2.4W  |

# LED Driver


## USC4 PRO

### Lifetime VS Case Temperature

USC4-320280GA




USC4-600400GA




### Operation Window for programing

USC4-320280GA




USC4-600400GA




### Power Factor VS Output Power

USC4-320280GA



USC4-600400GA




# LED Driver


## USC4 PRO

### Total Harmonic Distortion VS Output Power

USC4-320280GA




USC4-600400GA




### Efficiency VS Output Power


USC4-320280GA



USC4-600400GA



### DIMMING CURVE




# LED Driver

## USC4 PRO

### Wiring Connection


- **Module Temperature Protection (MTP)**

The LEDs are thermally protected by the driver's NTC (Negative Temperature Coefficient resistor) interface, which ensures the output current will be reduced when a critical temperature is reached. Connect an NTC on the LED module to the LED driver associated wires as shown in the wiring diagram below.



- **Programming Setup**


Programming doesn't require powering up input voltage or connecting the LED Module to the driver



# LED Driver USC4 PRO


## Dimensions

### USC4-320280GA



Unit: mm [inch]

### USC4-600400GA



Unit: mm [inch]

## Others

### Warranty Policy

Please reach out our [Warranty Policy](#) should you require any further clarification.