

工业电源

开架型电源

经济型

系列	型号名称*	PFC	输出				输入电压范围	尺寸 (毫米) (L × W × H)		
			电压	自然对流		强制风冷		开架型		
				电流	功率	电流		功率		
PJT  • 小尺寸 • 多种端子可选	PJT-12V40WBA□		12 V	3.33 A	40 W	-	-	90-264 V _{AC}	76.2 × 50.8 × 22.9	
	PJT-12V65WBA□			5.0 A	60 W	-	-		101.6 × 50.8 × 30	
	PJT-12V100WBA□	●		8.33 A	100 W	-	-		127 × 76.2 × 31	
	PJT-12V100WBB□			6.67 A	80 W	8.33 A	100 W		101.6 × 50.8 × 31.8	
	PJT-15V40WBA□		15 V	2.67 A	40 W	-	-	90-264 V _{AC}	76.2 × 50.8 × 22.9	
	PJT-15V65WBA□			4.2 A	63 W	-	-		101.6 × 50.8 × 30	
	PJT-15V100WBA□	●		6.67 A	100 W	-	-		127 × 76.2 × 31	
	PJT-15V100WBB□			5.33 A	80 W	6.67 A	100 W		101.6 × 50.8 × 31.8	
	PJT-18V40WBA□		18 V	2.22 A	40 W	-	-	90-264 V _{AC}	76.2 × 50.8 × 22.9	
	PJT-18V65WBA□			3.61 A	65 W	-	-		101.6 × 50.8 × 30	
	PJT-18V100WBA□	●		5.55 A	100 W	-	-		127 × 76.2 × 31	
	PJT-18V100WBB□			4.44 A	80 W	5.55 A	100 W		101.6 × 50.8 × 31.8	
	PJT-24V40WBA□		24 V	1.66 A	40 W	-	-	90-264 V _{AC}	76.2 × 50.8 × 22.9	
	PJT-24V65WBA□			2.71 A	65 W	-	-		101.6 × 50.8 × 30	
	PJT-24V100WBA□	●		4.17 A	100 W	-	-		127 × 76.2 × 31	
	PJT-24V100WBB□			3.33 A	80 W	4.17 A	100 W		101.6 × 50.8 × 31.8	




高性能

系列	型号名称*	PFC	输出			输入电压范围	尺寸 (毫米) (L × W × H)	
			电压	电流	功率		开架型	内置机壳型
PJ  • 多种可选配置 • 峰值功率达 200% / 10 秒 (≥ 100 W) • 支持 -40°C 冷启动 (≥ 100 W) • 三防胶涂布	PJ-5V15W□NA		5 V	3.0 A	15 W	85-264 V _{AC}	87.5 × 50 × 22	107.5 × 60 × 32
	PJ-12V15W□NA		12 V	1.3 A	15.6 W	85-264 V _{AC}	87.5 × 50 × 22	107.5 × 60 × 32
	PJ-12V30W□NA			2.5 A	30 W		105 × 50 × 25.6	125 × 60 × 36
	PJ-12V100W□RA	新品 ●		8.5 A	102 W		85-264 V _{AC} (直流输入范围 120-373 V _{DC})	155 × 62 × 27
	PJ-12V150W□RA	新品 ●		12.5 A	150 W		160 × 75 × 27	188 × 85 × 47
	PJ-24V30W□NA		24 V	1.25 A	31.2 W	85-264 V _{AC}	105 × 50 × 25.6	125 × 60 × 36
	PJ-24V100W□RA	新品 ●		4.3 A	103.2 W	85-264 V _{AC} (直流输入范围 120-373 V _{DC})	155 × 62 × 27	185 × 62 × 27
	PJ-24V150W□RA	新品 ●		6.3 A	151.2 W		160 × 75 × 27	188 × 85 × 47
	PJ-48V100W□RA	新品 ●	48 V	2.1 A	100.8 W	85-264 V _{AC} (直流输入范围 120-373 V _{DC})	155 × 62 × 27	185 × 62 × 27
	PJ-48V150W□RA	新品 ●		3.2 A	153.6 W		160 × 75 × 27	188 × 85 × 47
PJB  • 内置 PFC • 峰值功率达 200% / 10 秒 • 三防胶涂布	PJB-24V240W□□A	●	24 V	10.0 A	240 W	85-264 V _{AC}	180 × 84 × 42	212 × 98 × 59
	PJB-24V300W□□A	●		12.5 A	300 W			222 × 95 × 53.6

*对于可选项, 请参阅产品规格书

医疗电源

开架型电源

系列	型号名称	CC 代码	输入端子	输出端子	输出				尺寸 (毫米) (L × W × H)		
					电压	自然对流		强制风冷			
						电流	功率	电流		功率	
 <p>• 标准外型设计, 提供多种功率输出机型</p>	MDS-040APS12B	A	JST B2P3-VH	JST B4P-VH	12 V	3.33 A	40 W	-	-	76.2 × 50.8 × 23	
	MDS-065APS12B	A	JST B2P3-VH	JST B4P-VH		5.42 A	65 W	-	-	101.6 × 50.8 × 30	
	MDS-100APS12B	A	JST B2P3-VH	JST B8P-VH		8.33 A	100 W	-	-	127 × 76.2 × 31	
	MDS-100BPS12B	A	JST B2P3-VH	JST B4P-VH		6.67 A	80 W	8.33 A	100 W	101.6 × 50.8 × 31.8	
	MDS-250APB12	AA	Molex 26-62-4030	M3 PCB terminal		12.5 A	150 W	20.84 A	250 W	127.3 × 76.5 × 36.6	
		AB				12.5 A	150 W	20.84 A	250 W	127.3 × 76.5 × 36.6	
	MDS-300APB12	AA	Molex 26-62-4030	M3 PCB terminal		18.33 A	220 W	25.0 A	300 W	127.3 × 76.5 × 36.6	
	MDS-400APB12	AA	Molex 171813-9998	M3 PCB terminal		16.67 A	200 W	33.33 A	400 W	127.3 × 76.5 × 36.6	
		AB			16.67 A	200 W	33.33 A	400 W	127.3 × 76.5 × 36.6		
	MDS-040APS15B	A	JST B2P3-VH	JST B4P-VH	15 V	2.67 A	40 W	-	-	76.2 × 50.8 × 23	
	MDS-065APS15B	A	JST B2P3-VH	JST B4P-VH		4.2 A	65 W	-	-	101.6 × 50.8 × 30	
	MDS-100APS15B	A	JST B2P3-VH	JST B8P-VH		6.67 A	100 W	-	-	127 × 76.2 × 31	
	MDS-100BPS15B	A	JST B2P3-VH	JST B4P-VH		5.3 A	80 W	6.7 A	100 W	101.6 × 50.8 × 31.8	
	MDS-040APS18B	A	JST B2P3-VH	JST B4P-VH	18 V	2.22 A	40 W	-	-	76.2 × 50.8 × 23	
	MDS-065APS18B	A	JST B2P3-VH	JST B4P-VH		3.61 A	65 W	-	-	101.6 × 50.8 × 30	
	MDS-100APS18B	A	JST B2P3-VH	JST B8P-VH		5.55 A	100 W	-	-	127 × 76.2 × 31	
	MDS-100BPS18B	A	JST B2P3-VH	JST B4P-VH		4.4 A	80 W	5.5 A	100 W	101.6 × 50.8 × 31.8	
	MDS-300APB18	AA	Molex 26-62-4030	M3 PCB terminal		12.22 A	220 W	16.66 A	300 W	127.3 × 76.5 × 36.6	
		AB				12.22 A	220 W	16.66 A	300 W	127.3 × 76.5 × 36.6	
	MDS-040APS24B	A	JST B2P3-VH	JST B4P-VH		24 V	1.67 A	40 W	-	-	76.2 × 50.8 × 23
	MDS-065APS24B	A	JST B2P3-VH	JST B4P-VH			2.71 A	65 W	-	-	101.6 × 50.8 × 30
	MDS-100APS24B	A	JST B2P3-VH	JST B8P-VH	4.17 A		100 W	-	-	127 × 76.2 × 31	
	MDS-100BPS24B	A	JST B2P3-VH	JST B4P-VH	3.3 A		80 W	4.2 A	100 W	101.6 × 50.8 × 31.8	
	MDS-250APB24	AA	Molex 26-62-4030	M3 PCB terminal	6.25 A		150 W	10.41 A	250 W	127.3 × 76.5 × 36.6	
		AB			6.25 A		150 W	10.41 A	250 W	127.3 × 76.5 × 36.6	
	MDS-300APB24	AA	Molex 26-62-4030	M3 PCB terminal	10.0 A		240 W	12.5 A	300 W	127.3 × 76.5 × 36.6	
		AE			10.0 A		240 W	12.5 A	300 W	127.3 × 76.5 × 36.6	
	MDS-400APB24	AA	Molex 171813-9998	M3 PCB terminal	8.33 A		200 W	16.66 A	400 W	127.3 × 76.5 × 36.6	
AB		8.33 A			200 W		16.66 A	400 W	127.3 × 76.5 × 36.6		
MDS-200APB36	AA	Molex 171813-9998	JST B4P-VH	36 V	3.33 A		120 W	5.56 A	200 W	101.9 × 51.1 × 36.6	
MDS-300APB48	AA	Molex 26-62-4030	M3 PCB terminal	48 V	5.0 A		240 W	6.25 A	300 W	127.3 × 76.5 × 36.6	
	AB				5.0 A	240 W	6.25 A	300 W	127.3 × 76.5 × 36.6		
 <p>• 高功率密度, 外型小巧、低高度机身</p>	MEP-120A12J	BNA	JST B2P3-VH	JST B4P-VH	12 V	9.5 A	114 W	-	-	76.2 × 50.8 × 31	
	MEP-200A12J	BNA	JST B2P3-VH	JST B6P-VH-B		16.67 A*	200 W*	16.67 A	200 W	101.6 × 50.8 × 28.5	
	MEP-500A12J	BRA 新品	JST B2P3-VH	M4 PCB terminal		25.0 A	300 W	41.7 A	500 W	127 × 76.2 × 33.1	
	MEP-25A15J	BNA	JST B2P3-VH	JST B4P-VH	15 V	1.67 A	25 W	-	-	76.2 × 50.8 × 23	
	MEP-120A15J	BNA	JST B2P3-VH	JST B4P-VH		8.0 A	120 W	-	-	76.2 × 50.8 × 31	
	MEP-120A18J	BNA	JST B2P3-VH	JST B4P-VH	18 V	6.67 A	120 W	-	-	76.2 × 50.8 × 31	
	MEP-500A18J	BRA 新品	JST B2P3-VH	M4 PCB terminal		16.7 A	300 W	27.8 A	500 W	127 × 76.2 × 33.1	
	MEP-120A24J	BNA	JST B2P3-VH	JST B4P-VH		5.0 A	120 W	-	-	76.2 × 50.8 × 31	
	MEP-200A24J	BNA	JST B2P3-VH	JST B6P-VH-B	24 V	8.34 A*	200 W*	8.34 A	200 W	101.6 × 50.8 × 28.5	
	MEP-500A24J	BRA 新品	JST B2P3-VH	M4 PCB terminal		12.5 A	300 W	20.9 A	501 W	127 × 76.2 × 33.1	
	MEP-600A24J	BRA 新品	JST B2P3-VH	M4 PCB terminal		18.75 A	450 W	25.0 A	600 W	127 × 76.2 × 39	
	MEP-200A48J	BNA	JST B2P3-VH	JST B6P-VH-B	48 V	4.17 A*	200 W*	4.17 A	200 W	101.6 × 50.8 × 28.5	
MEP-500A48J	BRA 新品	JST B2P3-VH	M4 PCB terminal	6.25 A		300 W	10.5 A	504 W	127 × 76.2 × 33.1		
 <p>• U 型设计, 具备空气对流或强制通风冷却性能</p>	MEU-650A12T	AAA	DG128-7.5-03P-14-1001A(H)	M4 PCB terminal	12 V	33.4 A	400 W	50.0 A	600 W	152.4 × 101.6 × 40	
	MEU-600C24T	AAA	Anytek YK4020323200G	M5 PCB terminal	24 V	25.0 A	600 W	-	-	203.2 × 127 × 40	
	MEU-650A24T	AAA	DG128-7.5-03P-14-1001A(H)	M4 PCB terminal		18.75 A	450 W	27.1 A	650 W	152.4 × 101.6 × 40	
	MEU-600C48T	AAA	Anytek YK4020323200G	M5 PCB terminal	48 V	12.5 A	600 W	-	-	203.2 × 127 × 40	
	MEU-650A48T	AAA	DG128-7.5-03P-14-1001A(H)	M4 PCB terminal		9.375 A	450 W	13.6 A	650 W	152.4 × 101.6 × 40	

*参照产品技术数据手册