



中国国家强制性产品认证证书

证书编号：2025010907818729

认证委托人名称及地址

台达电子工业股份有限公司
台湾桃园市龟山区山顶里兴邦路 31 之 1 号

生产者名称及地址

台达电子工业股份有限公司
台湾桃园市龟山区山顶里兴邦路 31 之 1 号

生产企业名称及地址

台达电子印度股份有限公司-SEZ 单位
在勘察编号 16/1B2B 和 16/1B2A, 土地号一, 工业园区, 库鲁巴拉帕利村 克里斯赫纳吉里, 塔米尔纳杜, 635115, 印度

产品名称和系列、型号、规格

开关电源

型号: 1) DRF-24V960W1PBAX1X2; 2) DRF-960Z24V1PBX1X2X3; 3) DRL-24V960W1ENX1X2; 4) DRL-960Z24V1ENX1X2X3 ; 5) DRF-48V960W1PBAX1X2; 6) DRF-960Z48V1PBX1X2X3; 7) DRL-48V960W1ENX1X2; 8) DRL-960Z48V1ENX1X2X3; (X1, X2, X3 代表数字 0-9 或英文字母 A-Z 或空白, 其电气特性皆 相同, 只因客户不同, 给予不同名称, 不影响安全及电磁兼容性) 输入: 100-240VAC, 10.7A, 50-60Hz; 输出: 1) DC 24V, 40A (适用于型号: DRF-24V960W1PBAX1X2; DRF-960Z24V1PBX1X2X3; DRL-24V960W1ENX1X2; DRL-960Z24V1ENX1X2X3) 2) DC 48V; 20A (适用于型号: DRF-48V960W1PBAX1X2; DRF960Z48V1PBX1X2X3; DRL-48V960W1ENX1X2 DRL-960Z48V1ENX1X2X3) (不带电线组件销售, 仅适用于海拔 5000 米及以下)

产品标准和技术要求

GB 17625.1-2022 (A 类); GB 4943.1-2022; GB/T 9254.1-2021

上述产品符合《强制性产品认证实施规则 电子产品及安全附件》(CNCA-C09-01:2023) 的要求, 特发此证。

发证日期: 2025 年 10 月 16 日 有效期至: 2030 年 10 月 15 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验, 也可在认监委网站 (www.cnca.gov.cn) 查询。

经中国合格评定国家认可委员会认可 CNAS C001-P



签发:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2025010907818729

NAME AND ADDRESS OF THE APPLICANT

Delta Electronics, Inc.
No. 31-1, Xingbang Road, Shanding Village, Guishan District, Taoyuan City 333613, Taiwan ,
P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Delta Electronics, Inc.
No. 31-1, Xingbang Road, Shanding Village, Guishan District, Taoyuan City 333613, Taiwan ,
P.R.China

NAME AND LOCATION OF THE FACTORY

DELTA ELECTRONICS INDIA PRIVATE LIMITED - SEZ UNIT
SY No. 16/1B2B Part & 16/1B2A Part, Plot No.1, Industrial Park, Kurubarapalli Village, Krishnagiri
Dist, Tamil Nadu, 635115, India

PRODUCT NAME,MODEL AND SPECIFICATION

Switching Power Supply

Model : 1) The DRF-24H; 2) DRF-960Z24V1PBX1X2X3; 3) DRL-24V960W1ENX1X2; 4)
DRL-960Z24V1ENX1X2X3; 5) The DRF-48WX1Q; 6) DRF-960Z48V1PBX1X2X3; 7) DRL-48V1enx1x2; 8)
DRL-960Z48V1ENX1X2X3; (X1, X2,X3 represent numbers 0-9 or English letters A-Z or blank, their electrical
characteristics are all The same, only due to different customers, to different names, does not affect safety and
electromagnetic compatibility) Input: 100-240VAC, 10.7A, 50-60Hz; Output: 1) DC 24V, 40A (suitable for model:
DRF-24V960W1PBAX1X2; DRF-960Z24V1PBX1X2X3;DRL-24V960W1ENX1X2; DRL-960Z24V1ENX1X2X3) 2) DC
48V; 20A (suitable for model: DRF-48V960W1PBAX1X2; DRF960Z48V1PBX1X2X3;DRL-48V960W1ENX1X2
DRL-960Z48V1ENX1X2X3)(Sales without wire components) (Altitude up to 5000m)

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022 (class A) ;GB 4943.1-2022;GB/T 9254.1-2021

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C09-01:2023).

Valid from: Oct.16,2025

Valid until: Oct.15,2030

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

