





Industrial Power Supplies

DIN Rail Accessory Modules

Product Type	Series	Model Name ¹⁾	Output		Input Current	Input Voltage Range	Dimensions (mm) (H x W x D)		
			Voltage	Current					
Redundancy Module 	CliQ II	DRR-20A	22-60 V	20.0 A	(1+1 Redundancy) = Nominal 2 x 12.5 A (N+1 Redundancy) = Nominal 2 x 10 A	22-60 V _{DC}	121 x 50 x 122.1		
		DRR-20N					121 x 50 x 122.1		
		DRR-40A	22-60 V	40.0 A			(1+1 Redundancy) = Nominal 2 x 25 A (N+1 Redundancy) = Nominal 2 x 20 A	121 x 50 x 122.1	
		DRR-40N						121 x 50 x 122.1	
Buffer Module 	CliQ II	DRB-24V020AB□	24 V	20.0 A	Charging Mode: < 0.6 A	22.8-28.8 V _{DC}		121 x 70 x 120.1	
		DRB-24V040ABN						40.0 A	Charging Mode: < 0.6 A
DC-UPS Module 	CliQ II	DRU-24V40ABN	24 V	40.0 A	Charging Mode: 2.0 A ± 1.0 A	24-28 V _{DC}	121 x 50 x 117.3		
	CHROME	DRU-24V10ACZ	24 V	10.0 A	Charging Mode: 0.5 A ± 0.1 A	24-28 V _{DC}	91 x 71 x 55.6		
	CliQ M	DRU-24V10AMN	24 V	10.0 A	0.5 A, 1 A, 1.5 A, 2 A (typ.) (constant current)	18-30 V _{DC}	124 x 38 x 117		
		DRU-24V20AMN					20.0 A	0.75 A, 1.5 A, 2.25 A, 3 A (typ.) (constant current)	124 x 38 x 117
		DRU-24V40AMN							40.0 A

1) For options, please refer to the technical datasheet

Product Type	Series	Model Name	Nominal Voltage	Charging Current	Discharging Current	Dimensions (mm) (H x W x D)
Battery Module 	CliQ M	DRN-24V7AAEN	24 V	2.1 A Max	40.0 A Max	211.5 x 148 x 109.2